

## Technical data sheet: P-filament



Polypropylene (PP) is one of the most widely used plastics with a broad property profile. PP is one of the lightest materials and has excellent mechanical and chemical properties.

Material description	
Trade name	P-filament
Manufacturer	PPprint GmbH
Polymer group	Thermoplastic polymer
Chemical name	Polypropylene copolymer
Use	Extrusion-based 3D printing

Suggested 3D print settings (nozzle diameter 0.4 mm)	
Nozzle temperature	200 - 220 °C
Bed temperature	50 - 80 °C
Chamber temperature	recommended 50 - 80 °C
Bed modification	P-surface
Active fan cooling	recommended
Layer height	0.1 – 0.4 mm
Print speed	15 – 40 mm/s

Material properties		Test method
Melt temperature	137 °C	ASTM D3418
Melt Flow Rate <sup>1</sup>	19.3 g/10 min	ISO 1133
Melt Volume Rate <sup>1</sup>	25.7 cm <sup>3</sup> /10 min	ISO 1133
Density	0.9 g/cm <sup>3</sup>	ISO 1183
Odor	odorless	-
Color	natur	-

<sup>1</sup> Test condition: T = 210 °C; m = 5.0 kg

Mechanical properties: Tensile test		Test method ISO 527
All specimens were punched out of printed square tubes consisting of two shells, which were 3D printed with a Raise Pro 3D printer and applying the following printing conditions: Nozzle temperature: 210 °C; bed temperature: 70 °C; chamber temperature: 70 °C; printing speed: 30 mm/s.	90° 	0° 
	punched dog bone: S 3A with an orientation of 90 ° to the nozzle movement direction	punched dog bone: S 3A with an orientation of 0 ° to the nozzle movement direction
E-Modul (MPa)	640 ± 20	660 ± 10
Yield strength (MPa)	18.1 ± 0.1	19.6 ± 0.3
Tensile strength (MPa)	18.7 ± 0.3	35.1 ± 0.6
Strain at break (%)	> 600	> 600

<b>Certifications/approvals*</b>	<b>Description</b>
Regulation EU Nr. 10/2011	Union Guidelines on Regulation (EU) No 10/2011 on plastic materials and articles intended to come into contact with food (Europe)
FDA	Food and Drug administration approval (USA)

\* These data are generated using information obtained from the raw material suppliers.

<b>Filament specification</b>		<b>Test method</b>
Diameter 1.75	1.75 ± 0.10 mm	PPprint
Diameter 2.85	2.85 ± 0.10 mm	PPprint
Ovality	0.05	PPprint
Netto weight on spool	600 g ± 5%	PPprint

**Annotation:**

The data and properties presented here are averages of a standard batch. The 3D printed square tubes from which the specimens were punched out were produced in Slic3r version 1.3.0.

**Disclaimer:**

Acceptance of any technical information or assistance contained herein is at your own risk. PPprint GmbH makes no warranty with respect to or based on this information. PPprint GmbH is not liable for the use of this information or the mentioned products, processes or devices. It is your sole responsibility to determine their suitability and completeness for your individual application, for the protection of the environment as well as for the health and safety of your employees and buyers of your products. PPprint GmbH makes no warranty as to the marketability or suitability of the products and nothing herein constitutes a waiver of PPprint's Terms of Sale. Specifications are subject to change without notice.